Designation: E2995 - 15a (Reapproved 2020)

Standard Specification for ASTM Thermohydrometers with Integral Low-Hazard Thermometers¹

This standard is issued under the fixed designation E2995; the number immediately following the designation indicates the year of original adoption or, in the case of revision, the year of last revision. A number in parentheses indicates the year of last reapproval. A superscript epsilon (ε) indicates an editorial change since the last revision or reapproval.

1. Scope

- 1.1 This specification covers glass thermohydrometers of various scale graduation systems, intended for use in a variety of ASTM Test Methods.
- 1.2 The thermohydrometers presented in this standard are not exact replacements for the thermohydrometers in Specification E100; the thermometers have larger maximum permissible scale errors than do their Hg-filled counterparts. The user should decide if these thermohydrometers are appropriate for use in his or her application.
- 1.3 This standard does not purport to address all of the safety concerns, if any, associated with its use. It is the responsibility of the user of this standard to establish appropriate safety, health, and environmental practices and determine the applicability of regulatory limitations prior to use.
- 1.4 This international standard was developed in accordance with internationally recognized principles on standardization established in the Decision on Principles for the Development of International Standards, Guides and Recommendations issued by the World Trade Organization Technical Barriers to Trade (TBT) Committee.

2. Referenced Documents

2.1 ASTM Standards:²

D287 Test Method for API Gravity of Crude Petroleum and Petroleum Products (Hydrometer Method)

D1250 Guide for the Use of the Joint API and ASTM Adjunct for Temperature and Pressure Volume Correction Factors for Generalized Crude Oils, Refined Products, and Lubricating Oils: API MPMS Chapter 11.1

D3290 Specification for Bond and Ledger Papers for Perma-

E77 Test Method for Inspection and Verification of Thermometers

E100 Specification for ASTM Hydrometers

E126 Test Method for Inspection, Calibration, and Verification of ASTM Hydrometers

E344 Terminology Relating to Thermometry and Hydrometry

2.2 ISO Standard:⁴

ISO 1768:1975 Glass Hydrometers—Conventional Value for the Thermal Cubic Expansion Coefficient (for Use in the Preparation of Measurement Tables for Liquids)

3. Terminology

- 3.1 *Definitions:*
- 3.1.1 The definitions given in Terminology E344 apply.
- 3.2 Definitions of Terms Specific to This Standard:
- 3.2.1 *ledger paper*, *n*—a paper characterized by strength, high tearing resistance, eraseability, water resistance, ink receptivity, uniformity of surface, and smoothness.
- 3.2.1.1 *Discussion*—Originally, ledger paper was used especially for pen and ink records. Most ledger papers are surface sized, frequently subjected to appreciable wear, and must have a high degree of permanence and durability.
- 3.2.2 *length of the scale, n*—length of the nominal range in the stem, not including graduations extending above and below the nominal limits.
- 3.2.3 *thermohydrometer*, *n*—glass hydrometer having an integral thermometer.
- 3.2.4 top of the thermohydrometer, n—top of the finished instrument.
- 3.2.5 *total length*, *n*—overall length of the finished instrument.

nent Records (Withdrawn 2010)³


¹ This specification is under the jurisdiction of ASTM Committee E20 on Temperature Measurement and is the direct responsibility of Subcommittee E20.05 on Liquid-in-Glass Thermometers and Hydrometers.

Current edition approved May 1, 2020. Published May 2020. Originally approved in 1910. Last previous edition approved in 2015 as E2995-15a. DOI: 10.1520/E2995-15AR20

² For referenced ASTM standards, visit the ASTM website, www.astm.org, or contact ASTM Customer Service at service@astm.org. For *Annual Book of ASTM Standards* volume information, refer to the standard's Document Summary page on the ASTM website.

³ The last approved version of this historical standard is referenced on www.astm.org.

⁴ Available from International Organization for Standardization (ISO), ISO Central Secretariat, BIBC II, Chemin de Blandonnet 8, CP 401, 1214 Vernier, Geneva, Switzerland, http://www.iso.org.



4. Specifications

- 4.1 Thermohydrometers shall conform to the detailed specifications in Table 1 and to the general requirements specified in Sections 5 15.
- 4.2 Thermohydrometers shall conform to the inspection criteria found in Section 16 and the calibration and verification criteria found in Section 14.
- 4.3 Thermohydrometers manufactured to previous revisions of this specification shall retain the same ASTM status as those meeting current specifications.
- 4.4 At time of purchase, scale errors shall not exceed the maximum permissible scale error found in Table 1.

Note 1—Caution—Users should be aware that both temperature and density indications of thermohydrometers may change with rough handling, shock, exposure to aggressive liquids, and thermal cycling, among other factors. Consequently, test results and performance obtained at the time of manufacture may not necessarily apply throughout an extended period of use. Periodic calibration or verification of these instruments, in accordance with procedures set forth in Standard Test Method E126 (for the hydrometer), or Standard Test Method E77 (for the integral thermometer), is recommended.

5. Type

- 5.1 Thermohydrometers shall be of the constant mass, variable displacement type. Thermohydrometers shall be made of glass, except for the scale, ballast, cement, and the thermometric liquid of the thermometer.
- 5.2 The outer surface of the stem and body shall be symmetrical about the vertical axis. There shall be no uneven or unnecessary thickening of the walls, and no abrupt changes or constrictions that would hinder thorough cleaning or tend to trap air bubbles when the instrument is immersed.
- 5.3 The thermohydrometer shall float with its axis vertical in the liquids for which it is intended.
- 5.4 The thermohydrometer shall be thoroughly dry on the inside when sealed. The top of the stem shall be neatly rounded without unnecessary thickening.
- 5.5 The glass shall be smooth, transparent, and free of bubbles, strain patterns, cracks, or other imperfections that might interfere with the use of the thermohydrometer. The glass shall adequately resist the reaction of chemical agents to which thermohydrometers may be exposed, and also shall have suitable thermal properties to permit its use over the range of temperatures to which it may be subjected. In general, glasses suitable for constructing the bulbs of thermometers are satisfactory for thermohydrometers.
- 5.6 These thermohydrometers shall be fabricated from sodalime glass tubing having a thermal cubical expansion coefficient of $(25 \pm 2) \times 10^{-6}$ per °C.

Note 2—The value of the thermal cubical expansion coefficient given above is consistent with the conventional value given in ISO 1768.

6. Body

6.1 The preferred shapes for thermohydrometers in this specification is shown in Fig. 1.

7. Ballast

- 7.1 Material used for ballast shall be secured to the lower part of the body, with no loose material of any sort inside the thermohydrometer. When cement is used to hold the ballast securely in place, this cement shall not soften below 105 °C (221 °F).
- 7.2 If shot is used and sealed with wax, the wax shall not soften below $105 \, ^{\circ}\text{C}$ (221 $^{\circ}\text{F}$).

8. Stem

8.1 The stem shall be uniform in cross section, with no perceptible irregularities. It shall extend at least 15 mm above the top graduation, and remain cylindrical for at least 3 mm below the lowest graduation.

9. Scale

9.1 The material for the scale is not specified. However, if paper is used, ledger paper, meeting the specifications in Specification D3290, shall be used. The scale may be anchored by a design which prevents it from moving; otherwise it shall be fixed in place with a cement that will not soften below 105 °C (221 °F) and will not deteriorate with time. The paper shall show no evidence of scorching or charring when received, or after use at 105 °C (221 °F). The scale shall be straight and without twist.

10. Markings

- 10.1 Graduation lines and inscriptions shall be in a permanent black marking material, such as India ink.
- 10.2 All graduation lines shall be straight, fine lines not exceeding one fifth of the graduation interval in thickness, and in no case more than 0.2 mm. The lines shall be perpendicular to the vertical axis of the thermohydrometer. The lengths of main division lines, subdivision lines, and intermediate lines, if used, shall be chosen so as to facilitate readings. The shortest lines shall be at least 2 mm long.
 - 10.3 Identification of scale increments.
- 10.3.1 Scale graduations shall be numbered at ten scale division increments.
- 10.3.2 The numeric values displayed on the numbered scale graduations of API thermohydrometers shall be complete values corresponding to the indicated API value.
- 10.3.3 The numeric values displayed on the numbered scale graduations of density thermohydrometers shall be complete values at 50 kg/m³ intervals. Numeric values appearing on intermediate numbered scale divisions may be abbreviated.
- 10.3.4 The numeric values displayed on the numbered scale of the thermometer shall be complete values.
- 10.3.5 Scale Slippage Indicator—There shall be a permanent reference mark on the stem of the thermohydrometer corresponding to the first numbered scale graduation. An etched mark on the stem corresponding to the first numbered graduation on the scale, an ink line on the inside of the stem corresponding to the first numbered graduation on the scale, or a length of red glass fused to the inside top of the stem and




TABLE 1 Specifications for ASTM Thermohydrometers

API Gravity Thermohyd for Petroleum Products and Other Liquids of Similar S	
Thermometer Scale in	
ASTM Thermohydrometer No.	Nominal API Gravity Range, deg
S550HL-14	-6 to +6
S551HL-14	-1 to 11
S552HL-14	9 to 21
S553HL-14	19 to 31
S554HL-14	29 to 41
S555HL-14	39 to 51
S556HL-14	49 to 61
S557HL-14	59 to 71
S558HL-14	69 to 81
S559HL-14	79 to 91
S560HL-14	89 to 101
S561HL-14	37 to 49
S562HL-14	64 to 76
Thermohydrometer Dim	nensions
Total length, mm	374 to 387
Body diameter, mm	18 to 25
Stem diameter, min, mm	4.0
Hudromotor Sool	0
Hydrometer Scal Standard temperature, °F	60
Subdivisions, °API	0.1
Intermediate lines at, °API	0.5
Main (numbered) lines at, °API	1.0
Scale error at any point not to exceed, °API	0.1
Length of nominal scale, mm	125 to 145
Longar of Horimia coals, min	120 to 110
Thermometer Sca	
Range, °F	0 to 150
Immersion I I VII D Call U	total
Subdivisions, °F	2
Intermediate lines at, °F	10
Main (numbered) lines at, °F	
Scale error at any point not to exceed, °F	2
Scale length, mm	80 to 110
Document Pr	eview
Density Thermohydro for Petroleum Products and Other Liquids of Similar S	
Thermometer Scale in	n Body
ASTM Thermohydrometer No. ASTM F2005_15a(2	Nominal Range, kg/m³ at 15 °C
\$500HL-14	600 to 650
s://standards.iteh.ai/cat \$501HL-14\dards/sist/b57e09d7-5235-4a	600 to 650 a94-a2ae-db9e590 650 to 700 stm-e2995-15a2020
	600 to 650
s://standards.iteh.ai/cat \$501HL-14\dards/sist/b57e09d7-5235-4a	600 to 650 a94-a2ae-db9e590 650 to 700 stm-e2995-15a2020
:://standards.iteh.ai/eat.\$501HL-14ndards/sist/b57e09d7-5235-4a \$502HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750
s://standards.iteh.ai/cat.\$501HL-14.dards/sist/b57e09d7-5235-4a \$502HL-14 \$503HL-14 \$504HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850
s://standards.iteh.ai/cat.\$501HL-14.dards/sist/b57e09d7-5235-4a \$502HL-14 \$503HL-14 \$504HL-14 \$505HL-14	600 to 650 494-42ae-4b96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900
s://standards.iteh.ai/cat/S501HL-14ndards/sist/b57e09d7-5235-4a S502HL-14 S503HL-14 S504HL-14 S505HL-14 S506HL-14	600 to 650 494-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950
s://standards.iteh.ai/eat.\$501HL-14.dards/sist/b57e09d7-5235-4a \$502HL-14 \$503HL-14 \$505HL-14 \$506HL-14 \$507HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000
S502HL-14 S502HL-14 S503HL-14 S503HL-14 S505HL-14 S505HL-14 S506HL-14 S507HL-14 S508HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050
c://standards.iteh.ai/eat.\$501HL-14.dards/sist/b57e09d7-5235-4a \$502HL-14 \$503HL-14 \$505HL-14 \$506HL-14 \$507HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000
S502HL-14 S502HL-14 S503HL-14 S504HL-14 S505HL-14 S506HL-14 S507HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825
S//standards.iteh.ai/cat.S501HL-14.dards/sist/b57e09d7-5235-44 S502HL-14 S503HL-14 S505HL-14 S506HL-14 S506HL-14 S508HL-14 S509HL-14 S509HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825
SS/standards.iteh.ai/cat.S501HL-14.dards/sist/b57e09d7-5235-44 S502HL-14 S503HL-14 S505HL-14 S506HL-14 S507HL-14 S508HL-14 S509HL-14 S509HL-14 S510HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825
\$5/\standards.iteh.ai/cat\\$501HL-14\dards/\\$ist/b57e09d7-5235-4a\\ \$502HL-14\\ \$503HL-14\\ \$504HL-14\\ \$505HL-14\\ \$506HL-14\\ \$507HL-14\\ \$507HL-14\\ \$508HL-14\\ \$509HL-14\\ \$510HL-14\\ \$510HL-14\\ \$509HL-14\\ \$509HL-14\\ \$509HL-14\\ \$510HL-14\\ \$510HL-14\\ \$500HL-14\\	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825
\$\frac{\standards.iteh.ai/cat.\s501\text{HL-14\dards/\sist/b57e09d7-5235-4at}}{\s502\text{HL-14}} \s503\text{HL-14}} \s504\text{HL-14}} \s506\text{HL-14}} \s506\text{HL-14}} \s506\text{HL-14}} \s507\text{HL-14}} \s508\text{HL-14}} \s509\text{HL-14}} \s509\text{HL-14}} \s510\text{HL-14}} \s510\text{HL-14}}	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825
S502HL-14 S503HL-14 S503HL-14 S504HL-14 S506HL-14 S506HL-14 S506HL-14 S506HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0
S502HL-14 S503HL-14 S503HL-14 S504HL-14 S506HL-14 S506HL-14 S506HL-14 S506HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 enersions 374 to 387 18 to 25 4.0
Standards.iteh.ai/cat.S501HL-14.dards/sist/b57e09d7-5235-4d. S502HL-14 S503HL-14 S505HL-14 S505HL-14 S507HL-14 S508HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-14	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0
S502HL-14 S503HL-14 S503HL-14 S503HL-14 S505HL-14 S505HL-14 S507HL-14 S507HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0
S502HL-14 S503HL-14 S503HL-14 S503HL-14 S505HL-14 S505HL-14 S507HL-14 S507HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-16 S10HL-14 S509HL-16 S10HL-16 S10HL-17 S10HL-18 S10HL-19 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C	600 to 650 a94-a2ae-db9650 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5
S//standards.iteh.ai/cat.S501HL-14ndards/sist/b57e09d7-5235-4acccs502HL-14ccs503HL-14ccs503HL-14ccs505HL-14ccs	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 15 0.5 1.0 5 10
S502HL-14 S503HL-14 S504HL-14 S504HL-14 S506HL-14 S506HL-14 S506HL-14 S508HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Main (numbered) lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C	600 to 650 a94-a2ae-db96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 enersions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5
S5//standards.iteh.ai/cat.S501HL-14ndards/sist/b57e09d7-5235-4accs502HL-14cs503HL-14ds503HL-14ds505HL-14ds505HL-14ds507HL-14ds507HL-14ds509HL-14ds509HL-14ds509HL-14ds510HL-14ds	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 15 0.5 1.0 5 10
Standards.iteh.ai/cat.S501HL-14.dards/sist/b57e09d7-5235-4accs/standards.iteh.ai/cat.S501HL-14ccs/s503HL-14ccs/s505HL-14ccs/s505HL-14ccs/s505HL-14ccs/s505HL-14ccs/s509HL-14cc	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145
S502HL-14 S503HL-14 S503HL-14 S505HL-14 S506HL-14 S506HL-14 S507HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal Thermometer Scal	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145
S/standards.iteh.ai/cat.S501HL-14.dards/sist/b57e09d7-5235-4a. S502HL-14 S503HL-14 S504HL-14 S506HL-14 S507HL-14 S508HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal	600 to 650 a94-a2ae-db9e590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 10 0.5 125 to 145
S502HL-14 S503HL-14 S504HL-14 S504HL-14 S506HL-14 S506HL-14 S506HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal Range, °C Immersion	600 to 650 a94-a2ae-db96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145
S502HL-14 S503HL-14 S504HL-14 S504HL-14 S506HL-14 S506HL-14 S506HL-14 S508HL-14 S509HL-14 S509HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Main (numbered) lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal Range, °C Immersion Subdivisions, °C	600 to 650 a94-a2ae-db96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 enensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145 alle -20 to 65 total 1
S//standards.iteh.ai/cat.\$501HL-14ndards/sist/b57e09d7-5235-44 S502HL-14 S503HL-14 S505HL-14 S506HL-14 S507HL-14 S508HL-14 S509HL-14 S510HL-14 S510HL-14 S510HL-14 S510HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Main (numbered) lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal Range, °C Immersion Subdivisions, °C Intermediate lines at, °C	600 to 650 a94-a2ae-db96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 nensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145 alle -20 to 65 total 1 5
SSO2HL-14 SS03HL-14 SS03HL-14 SS06HL-14 SS06HL-14 SS06HL-14 SS08HL-14 SS09HL-14 SS09HL-14 SS09HL-14 SS10HL-14 SS10HL-14 SS10HL-14 SS10HL-15 Thermohydrometer Dim Total length, mm Body diameter, mm Stem diameter, min, mm Stem diameter, min, mm Hydrometer Scal Standardization temperature, °C Subdivisions, kg/m³ at 15 °C Intermediate lines, kg/m³ at 15 °C Number lines, kg/m³ at 15 °C Main (numbered) lines, kg/m³ at 15 °C Scale error at any point not to exceed, kg/m³ at 15 °C Length of nominal scale, mm Thermometer Scal Range, °C Immersion Subdivisions, °C	600 to 650 a94-a2ae-db96590 650 to 700 tm-e2995-15a2020 700 to 750 750 to 800 800 to 850 850 to 900 900 to 950 950 to 1000 1000 to 1050 1050 to 1100 775 to 825 enensions 374 to 387 18 to 25 4.0 le 15 0.5 1.0 5 10 0.5 125 to 145 alle -20 to 65 total 1