This document is not an ASTM standard and is intended only to provide the user of an ASTM standard an indication of what changes have been made to the previous version. Because it may not be technically possible to adequately depict all changes accurately, ASTM recommends that users consult prior editions as appropriate. In all cases only the current version of the standard as published by ASTM is to be considered the official document.



Designation: E879-01 (Reapproved 2007) Designation: E879 - 12

# Standard Specification for Thermistor Sensors for Clinical Laboratory Temperature MeasurementsThermistor Sensors for General Purpose and Laboratory Temperature Measurements<sup>1</sup>

This standard is issued under the fixed designation E879; the number immediately following the designation indicates the year of original adoption or, in the case of revision, the year of last revision. A number in parentheses indicates the year of last reapproval. A superscript epsilon ( $\varepsilon$ ) indicates an editorial change since the last revision or reapproval.

## 1. Scope

1.1 This specification covers the general requirements for <u>mNegative-t</u> <u>Temperature-e</u> <u>Coefficient (NTC)</u> thermistor-type sensors intended to be used for <u>elinical</u>-laboratory temperature measurements or control, or both, within the range from -10 to  $105^{\circ}$ C.

# 1.2 This specification also covers the detailed requirements for ASTM designated sensors.

1.3

<u>1.3 This specification also covers the requirements for general purpose, Negative Temperature Coefficient (NTC) thermistor-type sensors intended for use with Digital Contact Thermometers (also known as Digital Thermometers) within the range from -50 to  $+150^{\circ}$ C.</u>

<u>1.4</u> This standard does not purport to address all of the safety concerns, if any, associated with its use. It is the responsibility of the user of this standard to establish appropriate safety and health practices and determine the applicability of regulatory limitations prior to use.

## 2. Referenced Documents

2.1 ASTM Standards:<sup>2</sup>

E344 Terminology Relating to Thermometry and Hydrometry

E563 Practice for Preparation and Use of an Ice-Point Bath as a Reference Temperature

F29 Specification for Dumet Wire for Glass-to-Metal Seal Applications

## 3. Terminology

3.1 Definitions—The definitions given in Terminology E344 shall apply to this specification.

3.2 Definitions of Terms Specific to This Standard:

3.2.1 dissipation constant,  $\delta$ , *n*—the ratio of the change in energy dissipated per unit time (power) in a thermistor,  $\Delta P = P_2 - P_1$ , to the resultant temperature change of the thermistor,  $\Delta T = T_2 - T_1$ .

$$\delta = \frac{\Delta P}{\Delta T}$$
(1)

## E0879-12\_1

The dimensions of the dissipation constant are W/K.

For this specification,  $T_1$  is in the range from 20 to 38°C and  $\Delta T = 10$ °C.

3.2.2 *dumet*, *n*—round, copper-coated 42 % nickel-iron wire intended primarily for sealing to soft glass. Also known as CuNiFe in some communities.

3.2.3 *insulation resistance, dc, n*—the resistance at a specified direct-current voltage between the insulated leads of a thermistor sensor and the metallic enclosure of the sensor, if such an enclosure is present, or else between the sensor leads and a conductive medium in which the sensor is immersed.

3.2.4 *qualification test*, *n*—a series of tests conducted by the procuring agency or an agent thereof to determine conformance of thermistor sensors to the requirements of a specification, normally for the development of a qualified products list under the specification.

3.2.5 response time, n-the time required for a sensor to change a specified percentage of the total difference between its initial

Copyright © ASTM International, 100 Barr Harbor Drive, PO Box C700, West Conshohocken, PA 19428-2959, United States.

<sup>&</sup>lt;sup>1</sup> This specification is under the jurisdiction of ASTM Committee E20 on Temperature Measurement and is the direct responsibility of Subcommittee E20.03 on Resistance Thermometers.

Current edition approved May 1,  $\frac{2007}{2012}$ . Published June  $\frac{2007}{2012}$ . Originally approved in 1982. Last previous edition approved in  $\frac{2001}{2007}$  as E879 – 01 (2007). DOI: 10.1520/E0879-01R07.

<sup>&</sup>lt;sup>2</sup> For referenced ASTM standards, visit the ASTM website, www.astm.org, or contact ASTM Customer Service at service@astm.org. For Annual Book of ASTM Standards volume information, refer to the standard's Document Summary page on the ASTM website.

and final temperatures as determined from zero-power resistances when the sensor is subjected to a step function change in temperature.

E879 – 12

3.2.6 time constant, n-the 63.2 % response time of a sensor that exhibits a single-exponential response.

3.2.7 zero-power resistance, n-the dc resistance of a device, at a specified temperature, calculated for zero-power.

3.2.7.1 *Discussion*—Accurate zero-power resistance is obtained by extrapolating to zero-power the resistance values obtained from measurements at three or more levels of power with the sensor immersed in a constant temperature medium. For the purpose of this specification, this is obtained from measurements at a single power level adjusted such that the power is not greater than one-fifth the product of the dissipation constant specified in Table 1 (see 3.2.1 and 7.3) and the appropriate tolerance requirement of Table 2. When making stability measurements, the power shall be kept constant.

# 4. Classification

4.1 Thermistor sensors covered by this specification shall be classified with a type designation code that includes the ASTM detailed specification number followed by a descriptive code. See Fig. 1.

4.2 *ASTM Specification Number*—The ASTM specification number specifies uniquely the design and construction of the sensor including the type designation if more than one type appears in the same specification.

4.2.1 *Type Designation*—The type designation shall be a letter symbol to indicate the design and construction of the thermistor sensor.

4.2.1.1 Type S-Silicone rubber-coated glass probe with tinned Dumet extension leads (see Fig. 2).

4.2.1.2 Type E—Epoxy-coated glass probe with silver-plated copper extension leads (see Fig. 3).

4.2.1.3 Type G-General purpose four wire sensor in stainless steel housing (see Fig. 4).

4.2.1.4 Type H—General purpose two-wire sensor in stainless steel housing (see Fig. 5).

4.2.1.5 Type V—Interchangeable sensor enclosed in 1.2-mm vinyl tube (see Fig. 6).

4.2.1.6 Type W-Non-interchangeable sensor enclosed in 0.9-mm vinyl tube (see Fig. 7).

4.3 Operating Temperature Range—The operating temperature range shall be designated by a letter symbol (see Table 3).

4.4 Accuracy Class-The accuracy class shall be designated by a single-digit number (see Table 2).

4.5 Calibration Type—The type of calibration required for each unit shall be designated by a letter symbol. The letter I shall be used to denote units that are interchangeable with respect to a single resistance-temperature relationship. The letter N shall be used to denote non-interchangeable units for which resistance-temperature information must be furnished for each unit. For Calibration Type N sensors, serial number identification must be provided.

## 5. Requirements

**Document Preview** 

5.1 *Specifications*—Sensors shall comply with the general requirements specified herein as well as with the applicable detailed specifications of Table 1. In the event of conflict between this requirement paragraph and the detailed specification of Table 1, Figs. 2-7 the latter shall govern. <u>ASTM E879-12</u>

5.2 Zero-Power Resistance versus Temperature Relationship—The zero-power resistance versus temperature relationship shall be presented in a form such that any temperature within the specified operating temperature range can be obtained from that relationship and have an uncertainty no greater than one-tenth the specified tolerance in Table 2. When tested in accordance with 7.2, the zero-power resistance versus temperature relationship for interchangeable parts shall comply to within the tolerance specified in Table 2. The manufacturer of the sensor shall, for non-interchangeable parts, supply this relationship with each part shipped.

5.2.1 Accuracy—The resistance-temperature relationship, provided in Table 1, or with the sensor, or both, shall not differ from that obtained from measurements made in accordance with 7.2 by more than the tolerances specified in Table 2 for the applicable intervals specified in Table 1.

5.3 Thermal Requirements:

5.3.1 *Dissipation Constant*—When tested in accordance with 7.3, the dissipation constant shall be as specified in the detailed specification.

5.3.2 *Response Time*—When tested in accordance with 7.4, the response time or time constant, or both, shall be as specified in the detailed specification.

5.4 Environmental Requirements :

5.4.1 *Operating Temperature Range*—The operating temperature range shall be as specified in the type designation code (see 4.1 and 4.3).

5.4.2 *Storage Temperature Range*—Sensors shall be capable of meeting all requirements specified herein as well as those listed in the applicable detailed specification after storage at any temperature (or combination thereof) in the range from -40 to  $60^{\circ}$ C for a period of 1 year.

5.4.3 *Humidity Requirement*—Sensors shall be capable of being operated or stored at relative humidity from 0 to 95 % without condensation.

5.5 *Stability*:

5.5.1 *Short-Term Stability (10 days)*—When tested in accordance with 7.5.1, the equivalent temperature shift shall be no greater than 10 % of the tolerance shown in Table 2 for the accuracy class specified.

# €879 – 12

TABLE 1 Specification for ASTM Clinical Laboratory Thermistor Sensors

ASTM No.	E879 S B1N	E879 E B1N	E879 S B2N	E879 E B2N
Description	Silicone Rubber Coated Glass Probe	Epoxy Coated Glass Probe	Silicone Rubber Coated Glass Probe	Epoxy Coated Glass Probe
Major Application	General Purpose Clinical Laboratory Temperature Measurement	General Purpose Clinical Laboratory Temperature Measurement	General Purpose Clinical Laboratory Temperature Measurement	General Purpose Clinical Laboratory Temperature Measurement
Operating Temperature Range	–10 to 60 °C	-10 to 60 °C	–10 to 60 °C	-10 to 60 °C
Accuracy Class	1 (±0.01°C)	1 (±0.01°C)	2 (±0.02°C)	2 (±0.02°C)
Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range	–10 to 60 °C	–10 to 60 °C	–10 to 60 °C	–10 to 60 °C
Calibration Type Nominal <i>R-T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ (T in kelvins) $(T_0 \circ C) = [a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^{3}]^{-1} - 273.15$	Non-interchangeable	Non-interchangeable	Non-interchangeable	Non-interchangeable
Ao	-4.4495078	-4.4495078	-4.4495078	-4.4495078
A <sub>1</sub>	3614.7764	3614.7764	3614.7764	3614.7764
$A_2$	88190.906	88190.906	88190.906	88190.906
A <sub>3</sub>	-22328247	-22328247	-22328247	-22328247
a <sub>o</sub>	$0.11766716  imes 10^{-2}$	$0.11766716  imes 10^{-2}$	$0.11766716  imes 10^{-2}$	$0.11766716  imes 10^{-2}$
a <sub>1</sub>	$0.28173082  imes 10^{-3}$	$0.28173082  imes 10^{-3}$	$0.28173082  imes 10^{-3}$	$0.28173082  imes 10^{-3}$
a <sub>2</sub>	$-0.23285292  imes 10^{-5}$	$-0.23285292  imes 10^{-5}$	$-0.23285292  imes 10^{-5}$	$-0.23285292  imes 10^{-5}$
a <sub>3</sub>	$0.24131652 imes 10^{-6}$	$0.24131652 imes 10^{-6}$	$0.24131652 imes10^{-6}$	$0.24131652 imes 10^{-6}$
Type of Immersion Fluid	water, air	water, oil, air	water, air	water, oil, air
Nominal <i>R</i> o at 25°C	2.5 κΩ	2.5 κΩ	2.5κΩ	2.5 κΩ
Dissipation Constant	$3.5\pm0.9$ mW/K	5.0 $\pm$ 1.2 mW/K	3.5± 0.9 mW/K	$5.0 \pm 1.2 \text{ mW/K}$
53.2 % Response Time	$0.55 \pm 0.16 \ s$	$0.45 \pm 0.11 \text{ s}$	$0.55 \pm 0.16 \ s$	$0.45 \pm 0.11 \text{ s}$
Ratio of 95 % to 63.2 % Response Times	2.5 ± 0.6	2.1 ± 0.5	2.5 ± 0.6	2.1 ± 0.5
Design and Construction	Fig. 2	Fig. 3 Callual U	Fig. 2	Fig. 3
ASTM No.	E879 S A2N	E879 E A2N	E879 G B1N	E879 H B1N
Description	Silicone Rubber Coated Glass	langargs.n	5κΩ -4-Wire	5к $\Omega$ -2-Wire
	Probe	Epoxy Coated Glass Probe	Non-interchangeable Sensor in S.S. Housing	Non-interchangeable Sensor
Major Application	General Purpose Clinical Laboratory Temperature Measurement	General Purpose Clinical Laboratory Temperature Measurement	General Purpose Clinical Laboratory Temperature Measurement	in S.S. Housing General Purpose Clinical Laboratory Temperature Measurement
Operating Temperature Range	–10 to 105 °C	-10 to 105 °C 0_12	–10 to 60 °C	–10 to 60 °C
Accuracy Class	2 (±0.02°C)	2 (±0.02°C)	1 (±0.01°C)	1 (±0.01°C)
Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature	a-10 to 105°C tandards/sist	10 to 105 ℃ 015b-4b9c-	9–10 to 60°C 58bb64722	-10 to 60 °C 9-12
Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$	Non-interchangeable	Non-interchangeable	Non-interchangeable	Non-interchangeable
$T(°C) = [a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$				
	1 0000071	-4.3332947	-3.7563605	-3.7563605
	-4.3332974			
A <sub>1</sub>	4440.1603	4440.1603	3614.7764	3614.7764
4 <sub>1</sub> 4 <sub>2</sub>	4440.1603 -104525.78	4440.1603 -104525.78	88190.906	88190.906
4 <sub>1</sub> 4 <sub>2</sub> 4 <sub>3</sub>	4440.1603 -104525.78 -4581329.78	4440.1603 -104525.78 -4581329.78	88190.906 -22328247	88190.906 -22328247
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> a <sub>0</sub>	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup>	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup>	88190.906 -22328247 0.98019160 × 10 <sup>-3</sup>	88190.906 -22328247 0.98019160 × 10 <sup>-3</sup>
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> a <sub>0</sub> a <sub>1</sub>	4440.1603 -104525.78 -4581329.78 $0.98667965 \times 10^{-3}$ $0.24329879 \times 10^{-3}$	4440.1603 -104525.78 -4581329.78 0.98667965 $\times 10^{-3}$ 0.24329879 $\times 10^{-3}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \end{array}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \end{array}$
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> a <sub>0</sub> a <sub>1</sub> a <sub>2</sub>	$\begin{array}{l} 4440.1603 \\ -104525.78 \\ -4581329.78 \\ 0.98667965 \times 10^{-3} \\ 0.24329879 \times 10^{-3} \\ -0.59584872 \times 10^{-6} \end{array}$	4440.1603 -104525.78 -4581329.78 0.98667965 $\times 10^{-3}$ 0.24329879 $\times 10^{-3}$ -0.59584872 $\times 10^{-6}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \end{array}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \end{array}$
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> a <sub>0</sub> a <sub>1</sub> a <sub>2</sub> a <sub>3</sub>	4440.1603 -104525.78 -4581329.78 $0.98667965 \times 10^{-3}$ $0.24329879 \times 10^{-3}$	4440.1603 -104525.78 -4581329.78 0.98667965 $\times 10^{-3}$ 0.24329879 $\times 10^{-3}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \\ 0.24131652 \times 10^{-6} \\ \text{all fluids compatible with Type} \end{array}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \\ 0.24131652 \times 10^{-6} \\ \text{all fluids compatible with} \end{array}$
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> A <sub>0</sub> A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> Type of Immersion Fluid	4440.1603 -104525.78 -4581329.78 0.98667965 $\times 10^{-3}$ 0.24329879 $\times 10^{-3}$ -0.59584872 $\times 10^{-6}$ 0.97166167 $\times 10^{-7}$ water, air	$\begin{array}{c} 4440.1603 \\ -104525.78 \\ -4581329.78 \\ 0.98667965 \times 10^{-3} \\ 0.24329879 \times 10^{-3} \\ -0.59584872 \times 10^{-6} \\ 0.97166167 \times 10^{-7} \\ water, air \end{array}$	$\begin{array}{c} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with Type\\ 304 S.S. \end{array}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \\ 0.24131652 \times 10^{-6} \\ all fluids compatible with \\ Type 304 S.S. \end{array}$
A <sub>1</sub> A <sub>2</sub> A <sub>3</sub> a <sub>0</sub> a <sub>1</sub> a <sub>2</sub> a <sub>3</sub> Type of Immersion Fluid R <sub>0</sub> at 25°C	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup> 0.24329879 × 10 <sup>-3</sup> -0.59584872 × 10 <sup>-6</sup> 0.97166167 × 10 <sup>-7</sup> water, air 10κΩ	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup> 0.24329879 × 10 <sup>-3</sup> -0.59584872 × 10 <sup>-6</sup> 0.97166167 × 10 <sup>-7</sup> water, air 10 κΩ	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with Type\\ 304 S.S.\\ 5 κΩ \end{array}$	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with\\ Type 304 S.S.\\ 5\ \kappa\Omega \end{array}$
$A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid $R_0$ at 25°C Dissipation Constant	$\begin{array}{l} 4440.1603 \\ -104525.78 \\ -4581329.78 \\ 0.98667965 \times 10^{-3} \\ 0.24329879 \times 10^{-3} \\ -0.59584872 \times 10^{-6} \\ 0.97166167 \times 10^{-7} \\ water, air \\ 10\kappa\Omega \\ 3.5  \pm  0.9  mW/K \end{array}$	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup> 0.24329879 × 10 <sup>-3</sup> -0.59584872 × 10 <sup>-6</sup> 0.97166167 × 10 <sup>-7</sup> water, air 10 κΩ 5.0 $\pm$ 1.2 mW/K	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160 \times 10^{-3}\\ 0.28530667 \times 10^{-3}\\ -0.28303328 \times 10^{-5}\\ 0.24131652 \times 10^{-6}\\ all fluids compatible with Type 304 S.S.\\ 5 κΩ\\ 4.8\pm 1.2 \ mW/K \end{array}$	$\begin{array}{l} 88190.906 \\ -22328247 \\ 0.98019160 \times 10^{-3} \\ 0.28530667 \times 10^{-3} \\ -0.28303328 \times 10^{-5} \\ 0.24131652 \times 10^{-6} \\ all fluids compatible with \\ Type 304 S.S. \\ 5 \ \kappa\Omega \\ 4.8 \ \pm \ 1.2 \ mW/K \end{array}$
$\begin{array}{c} A_1 \\ A_2 \\ A_3 \\ a_0 \\ a_1 \\ a_2 \\ a_3 \\ \\ \text{Type of Immersion Fluid} \\ R_0 \text{ at } 25^\circ \text{C} \\ \text{Dissipation Constant} \\ 63.2 \ \% \text{ Response Time} \\ \text{Ratio of } 95 \ \% \text{ to } 63.2 \ \% \text{ Response} \end{array}$	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup> 0.24329879 × 10 <sup>-3</sup> -0.59584872 × 10 <sup>-6</sup> 0.97166167 × 10 <sup>-7</sup> water, air 10κΩ	4440.1603 -104525.78 -4581329.78 0.98667965 × 10 <sup>-3</sup> 0.24329879 × 10 <sup>-3</sup> -0.59584872 × 10 <sup>-6</sup> 0.97166167 × 10 <sup>-7</sup> water, air 10 κΩ	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with Type\\ 304 S.S.\\ 5 κΩ \end{array}$	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with\\ Type 304 S.S.\\ 5\ \kappa\Omega \end{array}$
$A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid $R_0$ at 25°C Dissipation Constant 63.2 % Response Time Ratio of 95 % to $63.2$ % Response Times Design and Construction	$\begin{array}{l} 4440.1603 \\ -104525.78 \\ -4581329.78 \\ 0.98667965 \times 10^{-3} \\ 0.24329879 \times 10^{-3} \\ -0.59584872 \times 10^{-6} \\ 0.97166167 \times 10^{-7} \\ water, air \\ \\ 10\kappa\Omega \\ 3.5 \pm 0.9 \ mW/K \\ 0.55 \pm 0.16 \ s \end{array}$	$\begin{array}{l} 4440.1603 \\ -104525.78 \\ -4581329.78 \\ 0.98667965 \times 10^{-3} \\ 0.24329879 \times 10^{-3} \\ -0.59584872 \times 10^{-6} \\ 0.97166167 \times 10^{-7} \\ water, air \\ 10 \ \kappa\Omega \\ 5.0 \ \pm \ 1.2 \ mW/K \\ 0.45 \ \pm \ 0.11 \ s \end{array}$	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with Type\\ 304 S.S.\\ 5\ \kappa\Omega\\ 4.8\pm\ 1.2\ mW/K\\ 4.5\ \pm\ 1.1\ s \end{array}$	$\begin{array}{l} 88190.906\\ -22328247\\ 0.98019160\times 10^{-3}\\ 0.28530667\times 10^{-3}\\ -0.28303328\times 10^{-5}\\ 0.24131652\times 10^{-6}\\ all fluids compatible with\\ Type 304 S.S.\\ 5\ \kappa\Omega\\ 4.8\ \pm\ 1.2\ mW/K\\ 4.5\ \pm\ 1.1\ s \end{array}$

5.5.2 Long-Term Stability (120 days)—When tested in accordance with 7.5.2, the equivalent temperature shift shall be no greater than 25 % of the tolerance shown in Table 2 for the accuracy class specified.

5.6 Low-Temperature Storage—When tested in accordance with 7.6, there shall be no evidence of mechanical damage and the


# €879 – 12

# TABLE 1 (continued)

ASTM No.	E879 G B1N	E879 H B1N	E879 G A2N	E879 H A2N
Description Major Application	10 κΩ 4-Wire Non- interchangeable Sensor in S.S. Housing General Purpose Clinical Laboratory Temperature Measurement	10 κΩ 2-Wire Non- interchangeable Sensor in S.S. Housing General Purpose Clinical Laboratory Temperature Measurement	10 κΩ 4-Wire Non- interchangeable Sensor in S.S. Housing General Purpose Clinical Laboratory Temperature Measurement	10 κΩ 2-Wire Non- interchangeable Sensor in S.S. Housing General Purpose Clinical Laboratory Temperature Measurement
Operating Temperature Range	-10 to 60 °C	–10 to 60 °C	–10 to 105 °C	–10 to 105 °C
Accuracy Class	1 (±0.01°C)	1 (±0.01°C)	2 (±0.02°C)	2 (±0.02°C)
Temperatures for Accuracy	–10 to 60 °C	–10 to 60 °C	–10 to 105 °C	–10 to 105 °C
Class Accuracies for other Temperatures Within Specified Temperature	9			
Range Calibration Type	Non-interchangeable	Non-interchangeable	Non-interchangeable	Non-interchangeable
Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ $T($ $^{\circ}C) = [a_0 + a_1LnR + a_2(LnR)^2 + A_3/T^2]$	Non-Interchangeable	Non-Interchangeable	Non-Interchangeable	Non-Interchangeable
a <sub>3</sub> ( <i>LnR</i> ) <sup>3</sup> ] <sup>-1</sup> – 273.15				
A <sub>o</sub>	-3.5684919	-3.5684919	-3.7191520	-3.7191520
$A_1$	3907.7065	3907.7065	4045.1666	4045.1666
A <sub>2</sub> A <sub>3</sub>	33480.382 -18666997	33480.382 -18666997	-8181.7100 -14472122	-8181.7100 -14472122
	$0.86972495 \times 10^{-3}$	$0.86972495 \times 10^{-3}$	-14472122 0.89898144 × 10 <sup>-3</sup>	-14472122 0.89898144 × 10 <sup>-3</sup>
a <sub>o</sub> a <sub>1</sub>	$0.27135335 \times 10^{-3}$	$0.27135335 \times 10^{-3}$	$0.26152805 \times 10^{-3}$	$0.26152805 \times 10^{-3}$
a <sub>2</sub>	$-0.20689100 \times 10^{-5}$	$-0.20689100 \times 10^{-5}$	$-0.97537969 \times 10^{-6}$	$-0.97537969 \times 10^{-6}$
a <sub>3</sub>	0.20547429 × 10 <sup>-6</sup>	$0.20547429  imes 10^{-6}$	$0.16613292 \times 10^{-6}$	$0.16613292  imes 10^{-6}$
Type of Immersion Fluid	all fluids compatible with Type	all fluids compatible with Type	all fluids compatible with Type	all fluids compatible with Type
	304 S.S.	304 S.S.	304 S.S.	304 S.S.
Nominal R <sub>0</sub> at 25 °C	10 κΩ		10 κΩ	10 κΩ
Dissipation Constant	$4.8 \pm 1.2 \text{ mW/K}$	4.8 ± 1.2 mW/K	4.8± 1.2 mW/K	$4.8 \pm 1.2 \text{ mW/K}$
63.2 % Response Time	4.5 ± 1.1 s	4.5 ± 1.1 s	4.5± 1.1 s	4.5 ± 1.1 s
Ratio of 95 % to 63.2 % Response Times	2.6 ± 0.3	2.6 ± 0.3	2.6 ± 0.3	2.6 ± 0.3
Design and Construction	Fig. 4	Fig. 5 Press	Fig. 4	Fig. 5
ASTM No.	E879 V B3I	E879 W B3N		
AOTIMINO.	L073 V D31	LOTS W DOIN		
Description	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube		
	Interchangeable Sensor Enclosed in 1.17 mm Plastic	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube	4b9c-99b9-63458bb64	722/astm-e879-12
Description	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Standard	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Candidard -10 to 60 °C 3 (±0.05°C)	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry -015b-4 -10 to 60 °C 3 (±0.05°C)	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Landard -10 to 60 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry -015b-4 -10 to 60 °C	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Landard -10 to 60 °C 3 (±0.05°C) 24 to 45°C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry -015b-4 -10 to 60 °C 3 (±0.05°C)	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tandard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry -015b-4 -10 to 60 °C 3 (±0.05°C)	4b9c-99b9-63458bb64	\$722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Within Specified Temperatures Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tandard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry -015b-4 -10 to 60 °C 3 (±0.05°C)	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Landard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tanclard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C Interchangeable	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ <i>T</i> ( °C) = [a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15 $A_0$ $A_1$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Landard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tanclard -10 to 60 °C 3 (±0.05°C) 24 to 45°C -10 to 24 °C: ±0.1 °C 45 to 60 °C: ±0.1 °C interchangeable	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry Landard -10 to 60 °C $3 (\pm 0.05^{\circ}C)$ 24 to 45°C -10 to 24 °C: $\pm 0.1 ^{\circ}C$ 45 to 60 °C: $\pm 0.1 ^{\circ}C$ Interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup>	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal $R$ - $T$ Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tanclard -10 to 60 °C $3 (\pm 0.05^{\circ}C)$ 24 to 45°C -10 to 24 °C: $\pm 0.1$ °C 45 to 60 °C: $\pm 0.1$ °C 45 to 60 °C: $\pm 0.1$ °C interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup>	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 0.78069589 × 10 <sup>-3</sup> 0.28967541 × 10 <sup>-3</sup>	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tancfare -10 to 60 °C $3 (\pm 0.05^{\circ}C)$ 24 to 45°C -10 to 24 °C: $\pm 0.1 ^{\circ}C$ 45 to 60 °C: $\pm 0.1 ^{\circ}C$ 45 to 60 °C: $\pm 0.1 ^{\circ}C$ Interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 $\times 10^{-3}$ 0.28128740 $\times 10^{-3}$ -0.25226292 $\times 10^{-5}$	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry $-015b-4$ -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 $0.78069589 \times 10^{-3}$ $0.28967541 \times 10^{-3}$ $-0.38427027 \times 10^{-5}$	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Within Specified Temperatures Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ <i>T</i> ( <sup>o</sup> C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ <i>A</i> <sub>0</sub> <i>A</i> <sub>1</sub> <i>A</i> <sub>2</sub> <i>A</i> <sub>3</sub> <i>a</i> <sub>0</sub> <i>a</i> <sub>1</sub> <i>a</i> <sub>2</sub> <i>a</i> <sub>3</sub>	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tancfare -10 to 60 °C $3 (\pm 0.05^{\circ}C)$ 24 to 45°C -10 to 24 °C: $\pm 0.1 ^{\circ}C$ 45 to 60 °C: $\pm 0.1 ^{\circ}C$ 45 to 60 °C: $\pm 0.1 ^{\circ}C$ 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup> -0.25226292 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-6</sup>	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry $-015b-4$ -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 $0.78069589 \times 10^{-3}$ $0.28967541 \times 10^{-3}$ $-0.38427027 \times 10^{-5}$ $0.24169639 \times 10^{-6}$	łb9c-99b9-63458bb64	\$722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ <i>T</i> ( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tancfare -10 to 60 °C 3 ( $\pm 0.05^{\circ}$ C) 24 to 45°C -10 to 24 °C: $\pm 0.1 ^{\circ}$ C 45 to 60 °C: $\pm 0.1 ^{\circ}$ C 45 to 60 °C: $\pm 0.1 ^{\circ}$ C mitterchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup> -0.25226292 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-6</sup> water	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 0.78069589 × 10 <sup>-3</sup> 0.28967541 × 10 <sup>-3</sup> -0.38427027 × 10 <sup>-5</sup> 0.24169639 × 10 <sup>-6</sup> water	łb9c-99b9-63458bb64	\$722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal $R$ - $T$ Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ $T($ <sup>°</sup> C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid Nominal $R_0$ at 25°C	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry standard -10 to 60 °C 3 ( $\pm$ 0.05°C) 24 to 45°C -10 to 24 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C mitterchangeable Interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup> -0.25226292 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-6</sup> water 11 κΩ	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry $-015b-4$ -10 to 60 °C 3 (±0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 $0.78069589 \times 10^{-3}$ $0.28967541 \times 10^{-3}$ $-0.38427027 \times 10^{-5}$ $0.24169639 \times 10^{-6}$ water 10 κΩ	łb9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal $R$ - $T$ Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid Nominal $R_0$ at 25°C Dissipation Constant	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tandard -10 to 60 °C 3 ( $\pm$ 0.05°C) 24 to 45°C -10 to 24 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C is to 60 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C -10 to 24 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 ( $\pm$ 0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperature Range Calibration Type Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = [a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15 $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid Nominal $R_0$ at 25°C Dissipation Constant 63.2 % Response Time	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tanclard -10 to 60 °C 3 ( $\pm$ 0.05°C) 24 to 45°C -10 to 24 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C interchangeable Interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup> -0.25226292 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-5</sup> water 11 κΩ 1.1 $\pm$ 0.3 mW/K 0.5 $\pm$ 0.12 s	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry $-015b-4$ -10 to 60 °C $3 (\pm 0.05°C)$ -10 to 60 °C Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 $0.78069589 \times 10^{-3}$ $0.28967541 \times 10^{-3}$ $-0.38427027 \times 10^{-5}$ $0.24169639 \times 10^{-6}$ water $10 \kappa\Omega$ $0.8 \pm 0.2 mW/K$ $0.26 \pm 0.06 s$	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Range Calibration Type Nominal $R$ - $T$ Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ T( °C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ $A_0$ $A_1$ $A_2$ $A_3$ $a_0$ $a_1$ $a_2$ $a_3$ Type of Immersion Fluid Nominal $R_0$ at 25°C Dissipation Constant	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tandard -10 to 60 °C 3 ( $\pm$ 0.05°C) 24 to 45°C -10 to 24 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C is to 60 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C -10 to 24 °C	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry - 015b-4 -10 to 60 °C 3 ( $\pm$ 0.05°C) -10 to 60 °C Non-interchangeable Non-interchangeable	4b9c-99b9-63458bb64	1722/astm-e879-12
Description Major Application Standards Operating Temperature Range Accuracy Class Temperatures for Accuracy Class Accuracies for other Temperatures Within Specified Temperatures Within Specified Temperatures Nominal <i>R</i> - <i>T</i> Characteristic $R = \exp[A_0 + A_1/T + A_2/T^2 + A_3/T^3]$ <i>T</i> ( <sup>o</sup> C) = $[a_0 + a_1LnR + a_2(LnR)^2 + a_3(LnR)^3]^{-1} - 273.15$ <i>A</i> <sub>0</sub> <i>A</i> <sub>1</sub> <i>A</i> <sub>2</sub> <i>A</i> <sub>3</sub> <i>a</i> <sub>0</sub> <i>a</i> <sub>1</sub> <i>a</i> <sub>2</sub> <i>a</i> <sub>3</sub> Type of Immersion Fluid Nominal <i>R</i> <sub>0</sub> at 25°C Dissipation Constant 63.2 % Response Time Ratio of 95 % to 63.2 % Response	Interchangeable Sensor Enclosed in 1.17 mm Plastic Tube Cuvette Thermometry tanclard -10 to 60 °C 3 ( $\pm$ 0.05°C) 24 to 45°C -10 to 24 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C 45 to 60 °C: $\pm$ 0.1 °C interchangeable Interchangeable -3.1645305 3763.4399 47816.278 -18332303 0.78686094 × 10 <sup>-3</sup> 0.28128740 × 10 <sup>-3</sup> -0.25226292 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-5</sup> 0.20852922 × 10 <sup>-5</sup> water 11 κΩ 1.1 $\pm$ 0.3 mW/K 0.5 $\pm$ 0.12 s	Non-interchangeable Sensor Enclosed in 0.92 mm Plastic Tube Cuvette Thermometry $-015b-4$ -10 to 60 °C $3 (\pm 0.05°C)$ -10 to 60 °C Non-interchangeable Non-interchangeable -3.0612396 3613.0051 88718.122 -22380305 $0.78069589 \times 10^{-3}$ $0.28967541 \times 10^{-3}$ $-0.38427027 \times 10^{-5}$ $0.24169639 \times 10^{-6}$ water $10 \kappa\Omega$ $0.8 \pm 0.2 mW/K$ $0.26 \pm 0.06 s$	4b9c-99b9-63458bb64	1722/astm-e879-12

🖽 E879 – 12

TABLE 2 Equivalent Temperature Tolerances for Different Class Sensors (See 4.1 and 4.4)



NOTE: METRIC [ ENGLISH ] ALL DIMENSIONS IN MILLIMETRES UNLESS OTHERWISE INDICATED.

FIG. 2 Silicone Rubber Coated Glass Probe

sensor shall comply with the accuracy requirements of 5.2.

5.7 *Thermal Shock*—When tested in accordance with 7.7, there shall be no evidence of mechanical damage and the sensor shall comply with the accuracy requirements of 5.2.

5.8 Insulation Resistance:


5.8.1 Dry Test—This requirement shall apply to sensors that have exposed metallic surfaces, but are not designed for immersion in conductive fluids. When tested in accordance with 7.8.1, there shall be no evidence of mechanical damage and the insulation resistance shall be sufficiently high that its shunting effect will not prevent the unit from complying with the accuracy requirement of Table 2. In no case shall the insulation resistance be less than  $10^8$  ohms.

5.8.2 *Wet Test*—This requirement shall apply to sensors that are designed for use in conductive solutions. When tested in accordance with 7.8.2, there shall be no evidence of mechanical damage and the insulation resistance shall be sufficiently high that its shunting effect will not prevent the unit from complying with the accuracy requirement of Table 2. In no case shall the insulation resistance be less than  $10^8$  ohms.

## 6. Quality Assurance Provisions

6.1 *General*—The methods of examination and tests con-tained in Section 7 are to be used to determine the conformance of sensors to the requirements of this specification. Each manufacturer or distributor who represents his products as conforming to this specification may, as agreed upon between the purchaser and seller, use statistically based sampling plans that are appropriate

🖽 E879 – 12



Note 1—Metric (English) All dimensions in millimetres unless otherwise indicated. FIG. 4 General Purpose Four-Wire Sensor in Stainless Steel Housing

for each inspection lot. Records shall be kept as necessary to document the claim that all of the requirements of this specification are met. The tests specified in this section are intended as minimum requirements. Additional sampling and testing of the product, as may be agreed upon between the purchaser and the seller, are not precluded by this section.

6.2 Classification of Inspection :

6.2.1 *Qualification Tests*—Qualification tests shall be performed for each basic design manufactured in accordance with this specification. The sample size required for the tests conducted shall be in accordance with Table 4. In order for a design to qualify, there shall be no failures resulting from any of the tests.

6.2.2 *Responsibility for Qualification Testing*—The manufacturer shall perform qualification testing, at least once, for each basic design for which this specification applies. If a basic design incorporates more than one resistance value of a specific material formulation or a particular style of thermistor, or both, different resistance values may be combined for the qualification sample. The highest and lowest resistance values for a specified thermistor design (type, material formulation, and geometry) must be included in the qualification sample. Qualification testing, by the manufacturer, must be repeated whenever a design change is introduced which may affect the performance of the sensor with regard to Section 5 of this specification.

6.2.3 *Manufacturing Screening Tests*—During manufacture, all parts produced in accordance with this specification shall receive 100 % testing for compliance with the requirements of Table 5.